

**IE- P I- RJ45- FJ- A**

<b>P</b>	Plug	<b>I</b>	Insert	<b>RJ45</b>	Copper insert RJ45	<b>TH</b>	Tool harnessing (crimp)	<b>A</b>	TIA 568 A color coding
<b>B</b>	Bulkhead	...		<b>24V</b>	Power 24 V	<b>FH</b>	Field harnessing (tool-free)	<b>B</b>	TIA 568 B color coding
...				<b>2SC</b>	FO plug insert SC	<b>FJ</b>	Field Jack (Module RJ45)	<b>P</b>	Profinet color coding
				<b>2LC</b>	FO plug insert LC	<b>C</b>	Coupling (2xRJ45)	<b>C</b>	Coupler
				<b>SCRJ2SC</b>	FO Adapter SCRJ auf SC	<b>A</b>	Angled	...	
				<b>SCRJ</b>	FO SCRJ insert	<b>S</b>	Straight		
				<b>LCD</b>	FO adaptor LC-Duplex	<b>MM</b>	MultiMode (if plug)		
				<b>USB-A</b>	USB-A coupling	<b>MM</b>	MultiMode / POF (if bulkhead)		
				<b>USB-3.0-A</b>	USB-A 3.0 coupling	<b>SM</b>	SingleMode		
				<b>USB-AB</b>	USB coupling A to B	<b>POF</b>	Plastic Optical Fiber		
				<b>HYP-10P</b>	Hybrid 10 pole insert	...			
				...					